

Model Code of Tube Shears (Example)

TCN-15

Tube Shears

⚠ Detailed Safety Instructions

Before using PISCO products, be sure to read "Safety Instructions" and "Safety Instruction Manual" on page 23 to 27 and "Common Safety Instructions for Tubes" on page 593 to 594.

Caution

1. Lock the safety lock when Tube Shears is not in use. There is a possibility of getting hurt from released edge. Do not carry it in a pocket. Safety lock can be unlocked unexpectedly by shakings or impacts.
2. Tube Shears can be used for PISCO Tubes only. Do not use it for cutting an electric wire or a steel pipe.

Applicable Tube

General PISCO Tubes

■ Tube for General Piping...Polyurethane Tube (P.596), Nylon Tube (P.608), Vacuum Tube (P.612)

■ Tube for Special Environments...Fluororesin (PFA) Tube (P.628), Polyamide Tube (P.634), Anti-spatter Tube (P.646), Anti-Static Tube (P.650), Fluororesin (PFA) Tube Clean-Room Package (P.638), Polyurethane Tube Clean-Room Package (P.642)

663

Standard Tube

Multi-core Tube

Coiling Tube

Twin Coiling Tube

Fluororesin / Polyamide Tube

Clean Room Tube

Anti-Spatter Tube

Anti-Static Tube

Tube Binder

Tube cutter

TCN-15 Tube Shears



● PISCO Tubes for pneumatic piping only

■ Tube Guide (Large)

mm size	ø10mm	ø12mm	ø16mm
inch size	ø3/8	ø1/2	ø5/8

■ Tube Guide (Small)

mm size	ø3mm	ø4mm	ø6mm	ø8mm	
inch size	ø1/8	ø5/32	ø3/16	ø1/4	ø5/16

